

EPDM sponge rubber cord is an ideal soft seal

ISO EPDM Terpolymre of ethylene, propylene and a diene (unsaturated diene in side chain)

Shape [shape_80](#)

Color Black

Material information

EPDM sponge rubber cord is available in many diameters for any type of application.

Usage examples

For example, as a seal on vacuum tables, or on two tubes pushed together, this material seals flexibly due to its low hardness.

Measurement tolerance 3302-1-E3

Item Overview

Item Code	Item Name	Width (mm)	Length (mm)
39000030	Sponsrubbersnoer 3 mm		200.000
39000040	Sponsrubbersnoer 4 mm		
39000050	Sponsrubbersnoer 5 mm		
39000060	Sponsrubbersnoer 6 mm		100.000
39000070	Sponsrubbersnoer 7 mm		
39000080	Sponsrubbersnoer 8 mm		100.000
39000090	Sponsrubbersnoer 9 mm		
39000100	Sponsrubbersnoer 10 mm		
39000120	Sponsrubbersnoer 12 mm		
39000130	Sponsrubbersnoer 13 mm		
39000140	Sponsrubbersnoer 14 mm		
39000150	Sponsrubbersnoer 15 mm		
39000160	Sponsrubbersnoer 16 mm		50.000
39000200	Sponsrubbersnoer 20 mm		25.000
39000250	Sponsrubbersnoer 25 mm		25.000
39000300	Sponsrubbersnoer 30 mm		20.000
39000400	Sponsrubbersnoer 40 mm		20.000
39000500	Sponsrubbersnoer 50 mm		10.000



Storage advice (ISO 2230)

The enclosed specification gives an indication of the storage periods to prevent degradation in properties of the material. Exposure to light and moisture should be avoided as much as possible. It is advisable to check the material in advance if it is to be stored for more than one year.

Group	Minimum temperature	Maximum temperature	Maximum humidity	Shelf life	Extension after inspection
C	10 °C	25 °C	65 %	10 year	5 year

We provide product information as known by us with great care. We cannot accept any liability for errors and/or inaccuracies and/or incompleteness. Please note that our products are intended for professional use only. For high impact applications and/or combinations of limit values we always recommend to have the properties specific to that situation verified by us. If there are multiple specifications for a product we will use the standard of 2mm or the closest specification.

